



### Colonnes analytiques SWxl et Super SW

| Description           | Réf.         | Ø <sub>int.</sub><br>(mm) | Longueur<br>(mm) | Porosité<br>(Å) | Granulométrie<br>(µm) | Efficacité<br>(plateaux/m) | Débit (ml/mn)<br>Rang. | Max   | Pression max.<br>(kg/cm <sup>2</sup> ) |
|-----------------------|--------------|---------------------------|------------------|-----------------|-----------------------|----------------------------|------------------------|-------|----------------------------------------|
| TSK-gel® G2000SWxl    | <b>08540</b> | 7,8                       | 300              | 125             | 5                     | > 20 000                   | 0,5 - 1,0              | 1,2   | 70                                     |
| TSK-gel® G3000SWxl    | <b>08541</b> | 7,8                       | 300              | 250             | 5                     | > 20 000                   | 0,5 - 1,0              | 1,2   | 70                                     |
| TSK-gel® G4000SWxl    | <b>08542</b> | 7,8                       | 300              | 450             | 8                     | > 16 000                   | 0,5 - 1,0              | 1,2   | 35                                     |
| TSK-gel® Super SW2000 | <b>18674</b> | 4,6                       | 300              | 125             | 4                     | > 30 000                   | 0,1 - 0,35             | 0,4   | 120                                    |
| TSK-gel® Super SW3000 | <b>18675</b> | 4,6                       | 300              | 250             | 4                     | > 30 000                   | 0,1 - 0,35             | 0,4   | 120                                    |
| TSK-gel® Super SW3000 | <b>21845</b> | 1,0                       | 300              | 250             | 4                     | > 18 000                   | 0,016                  | 0,02  | 120                                    |
| TSK-gel® Super SW3000 | <b>21485</b> | 2,0                       | 300              | 250             | 4                     | ≥ 25 000                   | 0,065                  | 0,075 | 120                                    |

### Colonnes préparatives SW

| Description      | Réf.         | Ø <sub>int.</sub><br>(mm) | Longueur<br>(mm) | Porosité<br>(Å) | Granulométrie<br>(µm) | Efficacité<br>(plateaux/m) | Débit (ml/mn)<br>Rang. | Max | Pression max.<br>(kg/cm <sup>2</sup> ) |
|------------------|--------------|---------------------------|------------------|-----------------|-----------------------|----------------------------|------------------------|-----|----------------------------------------|
| TSK-gel® G2000SW | <b>06727</b> | 21,5                      | 300              | 125             | 13                    | > 10 000                   | 3,0 - 6,0              | 8,0 | 10                                     |
| TSK-gel® G2000SW | <b>05146</b> | 21,5                      | 600              | 125             | 13                    | > 20 000                   | 3,0 - 6,0              | 8,0 | 20                                     |
| TSK-gel® G3000SW | <b>06728</b> | 21,5                      | 300              | 250             | 13                    | > 10 000                   | 3,0 - 6,0              | 8,0 | 15                                     |
| TSK-gel® G3000SW | <b>05147</b> | 21,5                      | 600              | 250             | 13                    | > 20 000                   | 3,0 - 6,0              | 8,0 | 30                                     |
| TSK-gel® G4000SW | <b>06729</b> | 21,5                      | 300              | 450             | 17                    | > 8 000                    | 3,0 - 6,0              | 8,0 | 10                                     |
| TSK-gel® G4000SW | <b>05148</b> | 21,5                      | 600              | 450             | 17                    | > 16 000                   | 3,0 - 6,0              | 8,0 | 20                                     |

### Colonnes de garde

| Description                     | Réf.         |
|---------------------------------|--------------|
| Colonne de garde SW             | <b>05371</b> |
| Colonne de garde SW en verre    | <b>08805</b> |
| Colonne de garde SWxl           | <b>08543</b> |
| Colonne de garde Super SW       | <b>18762</b> |
| Colonne de garde préparative SW | <b>05758</b> |

